

ChemMax® 3 uses the latest technology to produce a superior chemical protective product. Durable and lightweight, ChemMax® 3 provides a barrier against a broad spectrum of toxic industrial chemicals, dual-use chemicals, chemical warfare agents and other harmful contaminants.

The multi-layer film is applied to a heavy polypropylene nonwoven for increased strength and durability. The barrier film is significantly softer than other products on the market, resulting in a quiet, more comfortable garment.

ChemMax® 3 Coveralls



Coverall C3T110 Sealed Seam

- Collar
- Storm flap over zipper.
- Elastic wrists
- Elastic ankles Sizes: S – 5XL Case Pack: 6



Coverall C3T132 Sealed Seam

- Respirator-fit hood
- Zipper with storm flap
- Elastic face
- Elastic wrists
- Elastic ankles
 Sizes: S 5XL
 Case Pack: 6



Coverall C3T151

- Respirator-fit hood
- Storm flap over zipper
- Elastic face
- Elastic wristsAttached boots
- Sizes: S 5XL Case Pack: 6



Coverall C3T165

- Attached respirator-fit hood
- Double storm flap
- Hook and loop closure
- Elastic face and wrists
 - boot flaps Sizes: S – 5XL Case Pack: 6

· Attached boots with



Coverall C3T166

- Respirator fit hoodDouble storm flap
- over zipper
 Elastic wrists and
- ankles
 Velcro® closure over
- zipper Sizes: S – 5XL Case Pack: 6





ChemMax® 3 Brand Features

Excellent chemical barrier

Chemical warfare agent tested

Fabric is lighter weight and more flexible than all major competitors

ChemMax® 3 Configurations



Encapsulated Suit C3T400

- Rear entry/Flat back
- 48" zipper/Storm flap
- 20 mil Vinyl face shield
- Elastic wrists
- 1 exhaust port/shroud
- Air tube inlet
- Attached sock boots with boot flap
- Suit is not gas/vapor tight
 Sizes: S 5XL
 Case Pack: 1



Encapsulated Suit C3T450 – Level B

- Rear entry
- Expanded back
- 48" zipper
- Double storm flap20 mil Vinyl face shield
- Elastic wrists
- 2 exhaust ports/shroud
- Attached sock boots with boot flap
- Suit is not gas/vapor tight Sizes: S — 5XL Case Pack: 1



Hood Long Bib Style C3T716

- Long Bib Style
- 20 mil Vinyl lens
- 1" hook and loop side straps

Case Pack: 250



Jacket C3T250


- Collar
- Elastic wrists
- Double storm flap
- Hook and loop closure
 Sizes: S 5XL
 Case Pack: 6



Pant C3T320

- Elastic waist
- Elastic ankles
 Sizes: M-4X

Case Pack: 6



Boot Covers C3T740P

- Elastic top
- 17" high

Sizes: One size Case Pack: 12 pair

ChemMax® 3 Physical Properties

Property	Test Method	Units	Test Results
Basis Weight	ASTM D3776	oz./sq. yd	4.5
Grab Tensile MD	- ASTM D5034 -	pounds	58.7
Grab Tensile XD		pounds	42.2
Trapezoidal Tear MD	- ASTM D5733 -	pounds	25.6
Trapezoidal Tear XD		pounds	19.8
Ball Burst	ASTM D751	pounds	54.5
Surface Resistance	EN1149	Ω	Pass

Permeation Data for ASTM Recommended List of Chemicals for Evaluating Protective Clothing Materials (ASTM F1001)

Challenge Chemical	CAS Number	Physical State	Normalized Breakthrough
Acetone	67-64-1	Liquid	>480
Acetonitrile	75-05-8	Liquid	160
Ammonia Gas	7664-41-7	Gas	>480
1,3-Butadiene Gas	106-99-0	Gas	>480
Carbon Disulfide	75-15-0	Liquid	178
Chlorine Gas	7782-50-5	Gas	>480
Dichloromethane	75-09-2	Liquid	>480
Diethylamine	109-89-7	Liquid	imm.
Dimethyl Formamide	68-12-2	Gas	>480
Ethyl Acetate	141-78-6	Liquid	>480
Ethylene Oxide Gas	75-21-8	Gas	>480
n-Hexane	110-54-3	Liquid	>480
Hydrogen Chloride Gas	7647-01-0	Gas	>480
Methanol	67-56-1	Liquid	180
Methyl Chloride Gas	74-87-3	Gas	>480.
Nitrobenzene	98-95-3	Liquid	45
Sodium Hydroxide, 50%	1310-73-2	Liquid	>480
Sulfuric Acid, 98%	7664-93-9	Liquid	>480
Tetrachloroethylene	127-18-4	Liquid	>480
Tetrahydrofuran	109-99-9	Liquid	320
Toluene	108-88-3	Liquid	>480

ND = None Detected

> = greater than

L = liquid

G = ga

Numbers reported are averages of samples tested by the ASTM F739 test method. Sample results do vary and therefore averages for these results are reported.

Warnings

- ChemMax® 3 is not flame resistant and should not be used around heat, flame sparks, or in potentially flammable or explosive environments.
 Garments made of ChemMax® 3 should have slip resistant or anti-slip materials on the
- 2. Garments made of ChemMax® 3 should have slip resistant or anti-slip materials on the outer surface of boots, shoe covers or other garment surfaces in conditions where slipping could occur.

Note: Chemical Resistance Data is in accordance with ASTM F-739 test method. Testing is performed on fabric samples only, not finished garments. Sources for all test data are independent laboratory conditions and not actual use conditions.

