

Interceptor® Plus is the apex of Lakeland® Industries' chemical protective clothing line. Available in both Level A encapsulating, as well as non-encapsulating configurations, there is an Interceptor® Plus style for your needs be it gas, vapor, aerosol, liquids, harmful contaminants or particulate protection.

This next generation of Interceptor® fabric is now compatible with the PermaSURE® Toxicity Risk Modeller, giving you access to the most comprehensive chemical database in the industry.



PTFE visor process permanently seals the visor into the suit with no sewing involved so that liquids can't penetrate the visor edge

PTFE outer layer on visor prevents impairment of vision due to chemical contact

Attached gloves include non-reversing Silver Shield® inner glove with Butyl outer glove

Available in CE Type 1 certified Level A as well as non-encapsulating configurations



# Interceptor® Plus Configurations



#### INT640B INT640WB - Wide-View Face Shield

Blue CE Type 1:EN943:2005 Vapor tight (Level A) Deluxe Encapsulating Suit

- Fully encapsulated
- Front-entry
- Storage bag included Available in wide-view face shield configuration as PS80640W.

Sizes: S – 5X Case Pack: 1



#### INT650B INT650WB - Wide-View Face Shield

Blue CE Type 1:EN943:2005 Vapor tight (Level A) Deluxe Encapsulating Suit

- Fully encapsulated
- Rear-entry
- Storage bag included Available in wide-view face shield configuration as PS80650W.

Sizes: S – 5X Case Pack: 1



#### Interceptor Training Suit INT491B (Rear Entry) INT497B (Front Entry)

Encapsulated front or rear entry expanded back training suit.

- 20 Mil Vinyl lens
- 48" non separator cloth zipper that zips from bottom to top
- Zipper is reinforced at top and bottom with webbing on the outer side
- Double storm flap
- Exhaust port on back right side of hood
- 1 exhaust port on left back side of body
- Sock boots
- Boot flaps sewn on
- Vinyl gloves sewn on
- Internal belt loops and assembled belt
- No hem on splash guard or dump valve covers.

Training Use Only! Case Pack: 1



### INT620B

- Flat back front entry vapor-protective suit (Level A)
- Sealed seams on outside
- 48" zipper, double storm flap with hook and loop
- 2-layer faceshield (10 mil Teflon/40 mil Vinyl)
- Butyl gloves
- 2 exhaust valves
- Attached sock boots with boot flaps
- 1.5" waist belt with 3 belt loops sewn (inside) and sealed
- Storage bag included
  Sizes: S 5X
  Case Pack: 1



### Coverall INT165B

- · Attached respirator-fit hood
- Double storm flap
- Hook and loop closure
- Elastic face and wrists
  Attached boots with boots
- Attached boots with boot flaps

Sizes: S – 5X Case Pack: 3



## Coverall INT166B

- Respirator Fit Hood
- Double Storm Flap with hook and loop closure
- Elastic Wrists / Ankles
  Sizes: S 5X

Case Pack: 3

# **Interceptor® Plus Physical Properties**

Physical Property	Test Method Units		Test Results
Basis Weight	ASTM D3776	oz./sq. yd	11
Grab Tensile MD	ASTM D5034	lbs.	218.5 lbs.
Grab Tensile XD	ASTM D5034	lbs.	170.4 lbs.
Trapezoidal Tear MD	ASTM D5733	lbs.	34.7 lbs.
Trapezoidal Tear CD	ASTM D5733	lbs.	38.7 lbs.
Ball Burst	ASTM D3787	lbs.	250 lbs.

## Interceptor® Plus Permeation Testing - ASTM F1001

Chemical Name	Physi- cal Phase	Normalized Breakthrough Time (min.)	CAS No.
Acetone	L	>480	67-64-1
Acetonitrile	L	>480	75-05-8
Ammonia (gas)	G	>480	7664-41-7
1,3- Butadiene	G	>480	106-99-0
Carbon disulfide	L	>480	75-15-0
Chlorine gas	G	>480	7782-50-5
Dichloromethane	L	>480	75-09-2
Diethylamine	L	>480	109-89-7
N,N-Dimethylforma- mide	L	>480	68-12-2
Ethyl acetate	L	>480	141-78-6
Ethylene oxide	G	>480	75-21-8
n-Hexane	L	>480	110-54-3
Hydrogen chloride	G	>480	7647-01-0
Methanol	L	>480	67-56-1
Methyl chloride	G	>480	74-87-3
Nitrobenzene	L	>480	98-95-3
Sodium hydroxide, 50%	L	>480	1310-73-2
Sulfuric acid (conc.)	L	>480	7664-93-9
Tetrachloroethylene	L	>480	127-18-4
Tetrahydrofuran	L	>480	109-99-9
Toluene	L	>480	108-88-3

> = greater than, L = liquid, G = gas

**Note:** Chemical Resistance Data is in accordance with ASTM F-739 test method. Testing is performed on fabric samples only, not finished garments. Sources for all test data are independent laboratory conditions and not actual use conditions.



