

MicroMax® NS Cool Suit Features:

- SMS back panel increases breathablity and and provides a barrier to particulates and aerosol mist
- Elastic back waist provides improved comfort
- Front and sides material provides protection from dirt, liquids and light chemical splash
- Storm flap over zipper protects against splashes



MicroMax® NS Cool Suit Configurations



Coverall COL412 • Zipper closure

Sizes: S – 5X Case Pack: 25




Coverall COL428

- Zipper closure
- Attached hood
- Elastic wrists
- Elastic ankles

Sizes: S – 5X Case Pack: 25

The Cool Suit breathable back panel provides efficient cooling while the front and sides offer light barrier protection from liquids and splash

MicroMax® NS Cool Suit ... All-In-One Protection and Comfort!



MicroMax® NS Cool Suit Physical Properties

Physical Property	Test Method	Units	Test Results
Basis Weight	ASTM D3776	oz/y ²	1.85 oz/y ²
Strip Tensile MD	ASTM D5035	lbs.	11.3 lbs.
Strip Tensile XD	ASTM D5035	lbs.	6 lbs.
Tensile Strength MD	ASTM D5034	lbs.	24.4 lbs.
Tensile Strength XD	ASTM D5034	lbs.	16.2 lbs.
Trap/Tear MD	ASTM D1117	lbs.	10.8 lbs.
Trap/Tear XD	ASTM D1117	lbs.	5.4 lbs.
Ball Burst	ASTM 3787	lbs.	25.1 lbs.
Taber Abrasion	ASTM 3884	cycles	1062 cycles
Mocon-Breathability			5031
Air Permeability	ASTM D737	cfm/ft2	<0.562
Surface Resistance	EN1149	Ω	Pass
Hydrostatic Resistance	ASTM 4157	cfm	127+
Flammability Pass		lbs.	16 cfr 1610 cii

MicroMax® NS Cool Suit ASTM F903 Penetration Data

Chemical Tested	Concentra- tion %	Test Time – Minutes	Test Results
Diazinon (Roundup)	100%	60	Pass
Motor Oil-40 wt.	100%	60	Pass
Bleach-household	100%	60	Pass
Isocyanate Based Paint	100%	60	Pass
Sodium Hydroxide	50%	60	Pass
Sodium Hypochlorite	10%	60	Pass
Blood	Challenge Fluid Liter – 3.20 x 108 (PFU/mL)	Assay Results PFU/mL <1	Pass